

**Reltronix Ltd**

Trafalgar House
Tharston Industrial Estate
Norwich, Norfolk NR15 2PD
www.reltronix.com
sales@reltronix.com

Tel: +44(0)1603 859640

MIL PRF 38534 CLASS H TRAVELLER

Customer:SiS	Cust PO#:INTERNAL	Cust Spec:Man Data Sheet
LQH #:012	Bonding Diagram#: DBD005	SO:INTERNAL
Device:7808	Device IIL:6686	
Bond Wire:Au	Package Style:TO39	Package IIL:6821
Die Attach Type:Ag	Lid Style: TO39 CAP	Lid IIL:6821

SEQ	OPERATION/PS	CONDITIONS	QTY	ACCEPT	REJ.	DATE	SIG.	COMMENTS
1	100% Die Visual PS0001	MIL STD 883 TM 2010	15	15		23/6/23	DPB	Equipment #:1
2	Die Attach PS0002	Cure Epoxy 1Hr @150°C Oven Temp Check:152°C	15	15		23/6/23	DPB	Equipment #:8
3	Wire Bond PS 00003	Wire Type: Au Diameter: 1 Mils	15	15		23/6/23	DPB	Equipment #:7
4	Internal Visual PS0001	MIL STD 883 TM 2010	15	15		26/6/23	SE	Equipment #:1
5	Lid Seal PS 00004	Cure Epoxy 1Hr @150°C	15	15		26/6/23	SR	Equipment #:8 Oven Temp Check:150°C
6	100% Electrical Test +25°C	Manufacturers Datasheet	10	10		26/5/23	DPB	Equipment #:12 Program# 7808
7	100% Electrical Test -55°C	Manufacturers Datasheet	10	10		27/6/23	DPB	Equipment #:12 Program# 7808

ALL ELECTRICAL TEST RESULTS ARE SUPPLIED ELECTRONICALLY



Reltronix Ltd

Trafalgar House
Tharston Industrial Estate
Norwich, Norfolk NR15 2PD
www.reltronix.com
sales@reltronix.com
Tel: +44(0)1603 859640

SEQ	OPERATION/PS	CONDITIONS	QTY	ACCEPT	REJ.	DATE	SIG.	COMMENTS
8	100% Electrical Test +125°C	Manufacturers Datasheet	10	10		28/6/23	DPB	Equipment #:12 Program# 7808
9	Bond Pull Test Bake PS 00005	MIL STD 883 TM2011 1hr 300°C bake	10	10		28/6/23	DPB	Equipment #:8 Oven Temp Check# 300°C
10	Bond Pull Test PS 00006	MIL STD 883 TM2011 Attach Electronic Results to Folder	10	10		28/6/23	DPB	Equipment #:15 BPR:0030
11	Final QA PS 00001	Check Test Records and Documentation	10	10		29/6/23	DSB	
12	Dispatch goods and Electronic Records to customer		1	1		29/6/23	RB	
13								
14								

ALL ELECTRICAL TEST RESULTS ARE SUPPLIED ELECTRONICALLY

Data

Device #	Result	1 Vo 10V.5/500m	Vo 10.5V/5m	1 Vo10.5V/1	1 Vo 20V/5m	5.1 Vo 20V/1A	6.1 RegLine 1	7.1 RegLine 2	8.1 RegLoad 1	9.1 RegLoad 2	10.1 Iq	11.1 SVR	12.1 Isc
Unit		V	V	V	V	V	mV	mV	mV	mV	mA	dB	mA
Lower limit		7.700	7.700	7.700	7.700	7.700	-32.000	-16.000	-35.000	-35.000	0.000	68.000	0.00
Upper limit		8.300	8.300	8.300	8.300	8.300	32.000	16.000	35.000	35.000	8.000		1200.00
1	Pass	8.07	8.10	8.05	8.10	8.06	9.24	7.13	-27.36	-22.43	2.95	90.58	34.20
2	Pass	8.22	8.25	8.18	8.25	8.11	-8.18	5.40	-24.90	-32.46	3.04	90.75	47.60
3	Pass	8.10	8.12	8.07	8.12	8.07	-6.89	3.72	-27.09	-24.35	2.98	90.66	39.20
4	Pass	8.07	8.11	8.04	8.11	7.97	-6.19	6.31	-24.51	-31.46	3.00	90.58	37.30
5	Pass	7.96	8.13	7.89	8.13	8.03	24.26	11.09	-28.04	-22.71	-3.02	90.42	53.50
6	Pass	8.08	8.10	8.07	8.11	8.12	26.37	1.72	-30.83	-19.28	2.96	90.83	47.00
7	Pass	8.08	8.11	8.06	8.11	8.07	-27.38	4.00	-28.91	-22.29	3.08	90.83	39.30
8	Pass	8.06	8.10	8.02	8.10	8.00	-21.76	6.46	-29.26	-25.55	3.08	91.09	31.00
9	Pass	8.07	8.10	8.05	8.10	8.05	5.88	12.88	-29.29	-23.47	3.02	90.83	46.40
10	Pass	8.07	8.10	8.05	8.10	8.05	-1.23	4.14	-31.11	-24.58	3.02	91.01	35.10

Cust Spec :MAN. Data Sheet LQH #:012

TEMP =25°C

DEVICE: 7808



Data

Device #	Result	1 Vo 10V.5/500mA	Vo 10.5V/5mA	1 Vo10.5V/1A	1 Vo 20V/5mA	5.1 Vo 20V/1A	6.1 RegLine 1	7.1 RegLine 2	8.1 RegLoad 1	9.1 RegLoad 2	10.1 Iq	11.1 SVR	12.1 Isc
Unit		V	V	V	V	V	mV	mV	mV	mV	mA	dB	mA
Lower limit		7.700	7.700	7.700	7.700	7.700	-32.000	-16.000	-35.000	-35.000	0.000	68.000	0.00
Upper limit		8.300	8.300	8.300	8.300	8.300	32.000	16.000	35.000	35.000	8.000		1200.00
1	Pass	8.03	8.05	8.02	8.04	8.04	6.74	0.21	-28.92	-12.68	2.98	90.92	114.60
2	Pass	8.02	8.03	8.01	8.03	8.03	9.53	-0.74	-27.20	-13.35	2.92	91.01	138.00
3	Pass	8.02	8.04	8.01	8.04	8.04	5.26	1.54	-28.40	-14.44	2.94	90.83	185.90
4	Pass	8.02	8.03	8.01	8.03	8.03	7.14	4.05	-29.59	-8.54	2.93	91.36	197.90
5	Pass	8.04	8.05	8.04	8.05	8.11	19.59	-2.70	-29.34	-7.95	2.88	91.09	196.40
6	Pass	8.04	8.05	8.04	8.05	8.11	19.04	-1.76	-29.41	-8.63	2.88	91.09	199.90
7	Pass	8.04	8.06	8.02	8.06	7.96	-14.34	1.53	-28.57	-24.40	2.90	90.83	122.80
8	Pass	8.03	8.05	8.02	8.05	7.96	-14.98	0.80	-32.79	-24.06	2.87	91.09	129.60
9	Pass	8.03	8.04	8.02	8.04	8.05	17.59	-0.72	-28.67	-10.92	2.88	91.01	137.70
10	Pass	8.03	8.04	8.02	8.04	8.05	18.16	-0.75	-28.92	-13.30	2.87	90.83	141.40

Cust Spec :MAN. Data Sheet LQH #:012

TEMP =-55°C

DEVICE: 7808



Data

Device #	Result	1 Vo 10V.5/500m	1 Vo 10.5V/5m	1 Vo10.5V/1A	1 Vo 20V/5m	5.1 Vo 20V/1A	6.1 RegLine 1	7.1 RegLine 2	8.1 RegLoad 1	9.1 RegLoad 2	10.1 Iq	11.1 SVR	12.1 Isc
Unit		V	V	V	V	V	mV	mV	mV	mV	mA	dB	mA
Lower limit		7.700	7.700	7.700	7.700	7.700	-32.000	-16.000	-35.000	-35.000	0.000	68.000	0.00
Upper limit		8.300	8.300	8.300	8.300	8.300	32.000	16.000	35.000	35.000	8.000		1200.00
1	Pass	8.03	8.07	7.98	8.07	7.94	-31.41	13.51	-16.68	-28.89	2.81	90.83	13.70
2	Pass	8.02	8.07	7.98	8.07	7.95	-29.24	10.74	-18.76	-27.78	2.84	90.66	14.20
3	Pass	8.07	8.09	8.05	8.09	8.03	-29.44	8.80	-14.73	-18.61	2.88	90.34	17.20
4	Pass	8.06	8.08	8.04	8.08	8.03	-11.68	8.49	-14.06	-17.41	2.88	90.66	18.30
5	Pass	8.03	8.04	8.02	8.04	8.09	21.84	3.04	-15.21	-8.70	2.81	90.66	22.10
6	Pass	8.02	8.03	8.00	8.03	8.08	28.65	3.23	-19.59	-9.01	2.78	90.83	20.50
7	Pass	8.10	8.12	8.08	8.12	8.08	-8.21	4.01	-19.44	-20.78	2.97	91.18	38.00
8	Pass	8.09	8.11	8.06	8.11	8.04	-17.21	9.35	-11.07	-21.13	2.76	91.01	16.00
9	Pass	8.08	8.10	8.06	8.10	8.05	7.36	15.49	-16.15	-22.70	2.78	90.58	16.20
10	Pass	8.07	8.09	8.05	8.09	8.05	7.94	15.71	-18.84	-20.38	2.78	91.01	16.00

Cust Spec :MAN. Data Sheet

LQH #:012

TEMP =125°C

DEVICE: 7808



Part #	7808	Date	28 th June 2023
Sample Qty	5	Bond Type	Ball
Wire Size	25μ	Wire Type	Au
Min allowable strength	2.5gm	BPR	0030
Customer	SiS	Customer PO- SO	INTERNAL
Batch #	LQH0012	Equipment	XYZTEC

SN: 11			SN: 12			SN: 13			SN: 14			SN: 15					
#	F	C	#	F	C	#	F	C	#	F	C	#	F	C	#	F	C
1	9.22	8	3	6.92	8	5	9.09	8	7	8.66	8	9	7.64	8			
2	10.1	8	4	8.47	8	6	8.77	8	8	6.38	8	10	7.43	8			

F=Pull Strength in gms C=Failure Code

CODES

1. No Wire Break
2. Bond lift from Die
3. Bond lift from Post
4. Wire breaks at Heal
5. Die Metallisation delaminates
6. No Connection
7. Wire Breaks from Die
8. Bond Breaks at span